



Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
218	X1, X2, X3	1	
213	X1, X2, X3	2	
208	X1, X2, X3	3	
203	X1, X2, X3	4	
198	X1, X2, X3	5	

Secondary Volts

480			H1, H2, H3
277 1 phase			H1 to H0 H2 to H0 H3 to H0

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		LUG KIT	WEIGHT	PHASE	FREQUENCY
		LOW	HIGH				
150	T3150K0034B	208Δ	480Y/277		1188Lbs	3φ	60Hz
Temp Rise:	150°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	98.86%
Insulation:	220°C	Regulation @ 100% PF	1.60%	Windings:	AL	Typical No Load Losses:	348.11
NEMA ST20 Standard:	50dB	Standards:	UL/CSA	Impedance:	3.85%	100% Load (Typ) Load Losses (I ² R)	2823.03
Electrostatic Shield:	Option	Approvals:	DOE-16	Enclosure:	3R	Total Load Losses:	3171.14

Meets US DOE 2016 Efficiency

DATE: 14-Aug-13

TYPE NO:

CASE 4