





Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
480	H1, H2, H3	1	
456	H1, H2, H3	2	
432	H1, H2, H3	3	
Secondary Volts			
208			X1, X2, X3
120 1 phase			X1 to X0 X2 to X0 X3 to X0

NOTES:

1. KNOCKOUTS:

1.69 DIA. FOR 1.25 CONDUIT
1.13 DIA. FOR .75 CONDUIT



BOTTOM

Revisions

ACME  ELECTRIC

Type No.

DATE:

May 17, 2007

KVA	CATALOG NUMBER		VOLTAGE		WIRING DIAGRAM	WEIGHT	PHASE	FREQ.
			HIGH	LOW				
9.0	T-2A-53310-1S		480Δ	208Y/120		175 Lbs	3φ	60 Hz
	A	B	C	D	E	F	G	H
	17.77	15.28	11.17	12.71	15.27	14.03	15.15	11.52

A

PRINTS
TO

CONTROL
7