



Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
399	H1, H2, H3	1	
390	H1, H2, H3	2	
380	H1, H2, H3	3	
371	H1, H2, H3	4	
361	H1, H2, H3	5	
352	H1, H2, H3	6	
342	H1, H2, H3	7	
<b>Secondary Volts</b>			
220			X1, X2, X3
127			X1 to X0
1 phase			X2 to X0
			X3 to X0

KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
30	T-2A-79552-3S	380Δ	220Y127	WS-A-	365	3φ	50 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C
Insulation	220°C
Sound Level	45 dB

Windings:	AL
Standards	UL/CSA

Impedance	4.97%
-----------	-------

Typical Efficiency	97.23%
Full Load Losses	1,420w
No Load Losses	186w

ACME ELECTRIC

Type No.

						A	PRINTS TO	CONTROL	7	A
--	--	--	--	--	--	---	-----------	---------	---	---