


KEY: DENOTES CONDUIT AREAS



| Primary Volts | Connect Primary Lines To | Inter-Connect | Connect Secondary Lines To |
|-----------------|--------------------------|---------------|----------------------------|
| 504 | H1, H2, H3 | 1 | |
| 492 | H1, H2, H3 | 2 | |
| 480 | H1, H2, H3 | 3 | |
| 468 | H1, H2, H3 | 4 | |
| 456 | H1, H2, H3 | 5 | |
| 444 | H1, H2, H3 | 6 | |
| 432 | H1, H2, H3 | 7 | |
| Secondary Volts | | | |
| 240 | | | X1, X2, X3 |
| 120 | | | X1, X4 or X2, X4 |

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



| KVA | CATALOG NUMBER | VOLTAGE | | LUG KIT | WEIGHT | PHASE | FREQUENCY |
|-----------------------|----------------|---------------------------------|-------------------|------------|----------|--|-----------|
| | | HIGH | LOW | | | | |
| 225 | T3225K0023BS | 480 Δ | 240 Δ /120 | | 1500 Lbs | 3 ϕ | 60Hz |
| Temp Rise: | 150°C | TYPICAL PERFORMANCE DATA | | | | Typical Efficiency @ 35% | 99.02% |
| Insulation: | 220°C | Regulation @ 100% PF | 1.80% | Windings: | AL | Typical No Load Losses: | 485.60 |
| NEMA ST20 Standard: | 55 dB | Standards: | UL/CSA | Impedance: | 4.84% | 100% Load (Typ) Load Losses (I ² R) | 6075.47 |
| Electrostatic Shield: | Option | Approvals: | DOE-16 | Enclosure: | 3R | Total Load Losses: | 6561.07 |

Meets US DOE 2016 Efficiency

DATE: 11-Dec-15

TYPE NO:

CASE 4