



**REVISIONS**

**NOTES:**

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI




PRIMARY VOLTS	%	CONNECT LEADS TO TAP NO.
504	105	1
492	102.5	2
480	100	3
468	97.5	4
456	95	5
444	92.5	6
432	90	7



PRIMARY LINES TO H1-H2-H3  
SECONDARY LINES TO X0-X1-X2-X3

NOTE:  
PRIMARY AND SECONDARY BUS AREA  
IN FRONT OF CASE.



KEY: DENOTES CONDUIT AREAS

KVA	CATALOG NUMBER	VOLTAGE		K-FACTOR	WEIGHT	PHASE	FREQUENCY			
		HIGH	LOW							
30	T3030K0013BK13S	480Δ	208Y/120	13	500lbs	3φ	60Hz			
Temp Rise:	150°C	<b>TYPICAL PERFORMANCE DATA</b>				Typical Efficiency @ 35%				
Insulation:	220°C					Regulation @ 100% PF		Windings:	AL	Typical No Load Losses:
NEMA ST20 Standard:	45 dB					Standards:	UL/CSA	Impedance:		100% Load (Typ) Load Losses (I²R)
Electrostatic Shield:	YES					Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:

**Meets US DOE 2016 Efficiency**

DATE: 25-Jan-16

TYPE NO:

**CASE 2**