





KEY: DENOTES CONDUIT AREAS



Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
504	H1, H2, H3	1	
492	H1, H2, H3	2	
480	H1, H2, H3	3	
468	H1, H2, H3	4	
456	H1, H2, H3	5	
444	H1, H2, H3	6	
432	H1, H2, H3	7	

Secondary Volts

240			X1, X2, X3
120			X1, X4 or X2, X4

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		LUG KIT	WEIGHT	PHASE	FREQUENCY
		HIGH	LOW				
112.5	T3112K0023B	480Δ	240Δ/120		938 Lbs	3φ	60Hz
Temp Rise:	150°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	98.80%
Insulation:	220°C					Typical No Load Losses:	273.43
NEMA ST20 Standard:	50 dB					100% Load (Typ) Load Losses (I²R)	2216.93
Electrostatic Shield:	Option					Total Load Losses:	2490.35

Meets US DOE 2016 Efficiency

DATE: 14-Aug-13

TYPE NO:

CASE 3