


PRIMARY VOLTS	%	CONNECT LEADS TO TAP NO.
504	105	1
492	102.5	2
480	100	3
468	97.5	4
456	95	5
444	92.5	6
432	90	7



PRIMARY LINES TO H1-H2-H3  
SECONDARY LINES TO X0-X1-X2-X3

KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

## REVISIONS

### NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		LUG KIT	WEIGHT	PHASE	FREQUENCY
		HIGH	LOW				
300	T3300K0013BS	480Δ	208Y/120		1938 Lbs	3φ	60Hz
Temp Rise:	150°C	<b>TYPICAL PERFORMANCE DATA</b>				Typical Efficiency @ 35%	99.07%
Insulation:	220°C	Regulation @ 100% PF	1.70%	Windings:	AL	Typical No Load Losses:	471.43W
NEMA ST20 Standard:	60dB	Standards:	UL/CSA	Impedance:	4.74%	100% Load (Typ) Load Losses (I²R)	5543.22 W
Electrostatic Shield:	Option	Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:	6014.65W

DATE: 11-Jan-16

TYPE NO:

**CASE 5**

Meets US DOE 2016 Efficiency