




**REVISIONS**

**NOTES:**

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



PRIMARY VOLTS	%	CONNECT LEADS TO TAP NO.
504	105	1
492	102.5	2
480	100	3
468	97.5	4
456	95	5
444	92.5	6
432	90	7



PRIMARY LINES TO H1-H2-H3  
SECONDARY LINES TO X0-X1-X2-X3

KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KVA	CATALOG NUMBER	VOLTAGE		K-FACTOR	WEIGHT	PHASE	FREQUENCY
		HIGH	LOW				
150	T3150K0013BK20S	480Δ	208Y/120	20	1600 Lbs	3φ	60Hz
Temp Rise:	150°C	<b>TYPICAL PERFORMANCE DATA</b>				Typical Efficiency @ 35%	
Insulation:	220°C	Regulation @ 100% PF		Windings:	AL	Typical No Load Losses:	
NEMA ST20 Standard:	50dB	Standards:	UL/CSA	Impedance:		100% Load (Typ) Load Losses (I²R)	
Electrostatic Shield:	YES	Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:	

**Meets US DOE 2016 Efficiency**

DATE: 25-Jan-16

TYPE NO:

**CASE 4**