



**REVISIONS**

**NOTES:**

- 1. Dry Type
- 2. Class AA
- 3. Ventilated
- 4. Paint - #61 ANSI



| Primary Volts   | Connect Primary Lines To | Inter-Connect | Connect Secondary Lines To |
|-----------------|--------------------------|---------------|----------------------------|
| 504             | H1, H2, H3               | 1             |                            |
| 492             | H1, H2, H3               | 2             |                            |
| 480             | H1, H2, H3               | 3             |                            |
| 468             | H1, H2, H3               | 4             |                            |
| 456             | H1, H2, H3               | 5             |                            |
| 444             | H1, H2, H3               | 6             |                            |
| 432             | H1, H2, H3               | 7             |                            |
| Secondary Volts |                          |               |                            |
| 240             |                          |               | X1, X2, X3                 |
| 120             |                          |               | X1, X4 or X2, X4           |



KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.



| KVA                   | CATALOG NUMBER | VOLTAGE                         |          | LUG KIT    | WEIGHT   | PHASE                             | FREQUENCY |
|-----------------------|----------------|---------------------------------|----------|------------|----------|-----------------------------------|-----------|
|                       |                | HIGH                            | LOW      |            |          |                                   |           |
| 300                   | T3300K0023BS   | 480Δ                            | 240Δ/120 | Lug 3      | 1938 Lbs | 3φ                                | 60Hz      |
| Temp Rise:            | 150°C          | <b>TYPICAL PERFORMANCE DATA</b> |          |            |          | Typical Efficiency @ 35%          | 99.02%    |
| Insulation:           | 220°C          | Regulation @ 100% PF            | 1.80%    | Windings:  | AL       | Typical No Load Losses:           | 485.6W    |
| NEMA ST20 Standard:   | 55dB           | Standards:                      | UL/CSA   | Impedance: | 4.84%    | 100% Load (Typ) Load Losses (I²R) | 6075.5W   |
| Electrostatic Shield: | Option         | Approvals:                      | DOE-2016 | Enclosure: | 3R       | Total Load Losses:                | 6,561.1W  |

DATE: 11-Dec-15

TYPE NO:

**CASE 5**

**Meets US DOE 2016 Efficiency**