



Primary Volts	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
218	X1, X2, X3	1	
213	X1, X2, X3	2	
208	X1, X2, X3	3	
203	X1, X2, X3	4	
198	X1, X2, X3	5	

Secondary Volts			
480			H1, H2, H3
277			H1 to H0 H2 to H0 H3 to H0
1 phase			

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		LUG KIT	WEIGHT	PHASE	FREQUENCY
		LOW	HIGH				
225	T3225K0034B	208 Δ	480Y/277		1500 Lbs	3 ϕ	60Hz
Temp Rise:	150°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	98.94%
Insulation:	220°C	Regulation @ 100% PF	1.60%	Windings:	AL	Typical No Load Losses:	475.41
NEMA ST20 Standard:	55 dB	Standards:	UL/CSA	Impedance:	3.91%	100% Load (Typ) Load Losses (I ² R)	3964.61
Electrostatic Shield:	Option	Approvals:	DOE-16	Enclosure:	3R	Total Load Losses:	4440.02

Meets US DOE 2016 Efficiency

DATE: 14-Aug-13

TYPE NO:

CASE 4