



KEY: DENOTES CONDUIT AREAS

NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

REVISIONS

NOTES:

1. Dry Type
2. Class AA
3. Ventilated
4. Paint - #61 ANSI



KVA	CATALOG NUMBER	VOLTAGE		LUG KIT	WEIGHT	PHASE	FREQUENCY
		HIGH	LOW				
500	T3500K0013BS	480Δ	208Y/120			3φ	60Hz
Temp Rise:	150°C	TYPICAL PERFORMANCE DATA				Typical Efficiency @ 35%	99.17%
Insulation:	220°C	Regulation @ 100% PF	1.50%	Windings:	AL	Typical No Load Losses:	727.3W
NEMA ST20 Standard:		Standards:	UL/CSA	Impedance:	5.90%	100% Load (Typ) Load Losses (I²R)	7,896.9W
Electrostatic Shield:	Option	Approvals:	DOE-2016	Enclosure:	3R	Total Load Losses:	8,624.2W

DATE: 14-Aug-13

TYPE NO:

CASE 7

Meets US DOE 2016 Efficiency