

Project Number
17.02765



Date
10/13/2017

Lab 6
Sphere

Test Sample Description

Catalog Number: P5674-3130K
Description: 5" 17W LED Down-Light Cylinder

Photometry

Test Method: IES LM-79-08 § 10
Preburn Time: 1:00
Time To Stabilize: 3:00
Total Operating Time: 4:10

Input Voltage (Volts): 120.1
Input Current (Amps): 0.151
Input Wattage (Watts): 16.9
Ambient Temp (°C): 24.1

Sphere

Test Method: IES LM-79-08 § 9.1 & 12.1
Preburn Time: 8:00
Time To Stabilize: 1:05
Total Operating Time: 9:05

Input Voltage (Volts): 120.0
Input Current (Amps): 0.151
Input Wattage (Watts): 16.8
Ambient Temp (°C): 24.0
PF @ 120V: 0.93
THD @ 120V (%): 40.6



Hubbell Lighting, Inc.

701 Millennium Boulevard
Greenville, SC 29607
www.hubbellighting.com

Checked (sphere): B.LEE
Checked (photometry): M.ELLMANN
Approved: P. McCARTHY




This report shall not be used to claim product certification, approval, or endorsement by NVLAP, NIST, or any agency of the federal government.



Lamp Desc: 1 - 3000K LED Module

Efficacy: 29.8 LPW S/P Ratio: 1.5 LM/LM


Chromaticity Diagram



Spectral Results

Name	Value	Unit
Φ	1.65	watts
$\Phi(v)$	501	lumens
$\Phi(v')$	731	lm'
Chrom x	0.4313	
Chrom y	0.4009	
Chrom u	0.2483	
Chrom v	0.3462	
Duv	0.0005	
Chrom u'	0.2483	
Chrom v'	0.5193	
CCT	3069	K
Purity	49.8	%
λ (dom)	582.7	nm
FWHM	157.8	nm
λ (peak)	612.9	nm
λ (center)	589.1	nm
λ (centroid)	586.5	nm
SDCM	Cool White	
RA	93	
Corr. Coef.	0.000515798	
Correlation	0.0054	
R1	94.1	
R2	97.0	
R3	98.6	
R4	95.3	
R5	94.6	
R6	96.8	
R7	90.1	
R8	77.6	
R9	48.8	
R10	93.3	
R11	96.6	
R12	85.6	
R13	95.3	
R14	99.4	

Spectral Distribution of Radiant Flux



This report shall not be used to claim product certification, approval, or endorsement by NVLAP, NIST, or any agency of the federal government.



®

HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 17.02765

PAGE: 3 OF 12

ISSUE DATE: 10/18/17

PREPARED FOR: PROGRESS

CATALOG NUMBER: P5674-3130K

LUMINAIRE: 5" 17W LED Down-Light Cylinder

LAMP: 1 - 3000K LED Module

MOUNTING: Wall

NOTE: DATA SHOWN IS ABSOLUTE FOR THE SAMPLE PROVIDED.



HUBBELL
Lighting


701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 17.02765
ISSUE DATE: 10/18/17
PREPARED FOR: PROGRESS
CATALOG NUMBER: P5674-3130K

PAGE: 4 OF 12

ISOFOOTCANDLE LINES OF HORIZONTAL ILLUMINATION Values based on 6.5-foot mounting height

IES Classification: Type V
Cutoff Classification (deprecated): Full Cutoff






HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 17.02765
ISSUE DATE: 10/18/17
PREPARED FOR: PROGRESS
CATALOG NUMBER: P5674-3130K

PAGE: 5 OF 12

MAXIMUM PLANE AND MAXIMUM CONE PLOTS OF CANDELA






HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 17.02765
ISSUE DATE: 10/18/17
PREPARED FOR: PROGRESS
CATALOG NUMBER: P5674-3130K

PAGE: 6 OF 12

COEFFICIENTS OF UTILIZATION AND FLUX DISTRIBUTION



	LUMENS	PERCENT OF FIXTURE
DOWNWARD STREET SIDE	252	50.0
DOWNWARD HOUSE SIDE	252	50.0
DOWNWARD TOTAL	504	100.0
UPWARD STREET SIDE	0	0.0
UPWARD HOUSE SIDE	0	0.0
UPWARD TOTAL	0	0.0
TOTAL FLUX	504	100.0
EFFICACY = 29.8 lm/W		

ALL CANDELA AND LUMENS IN THIS REPORT ARE BASED ON ABSOLUTE PHOTOMETRY. THE COEFFICIENT OF UTILIZATION VALUES ARE BASED ON THE TOTAL ABSOLUTE LUMEN OUTPUT OF THIS LUMINAIRE SAMPLE.



HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 17.02765
ISSUE DATE: 10/18/17
PREPARED FOR: PROGRESS
CATALOG NUMBER: P5674-3130K

PAGE: 7 OF 12

BUG Rating Zonal Summary	Lumens	% of Fixture	Zone Ratings		
			B1	U0	G0
			B	U	G
Forward	252	50.0			
FL (0° – 30°)	142.7	28.3			
FM (30° – 60°)	106.6	21.1			
FH (60° – 80°)	2.7	0.5			G0
FVH (80° – 90°)	0.1	0.0			G0
Backward	252	50.0			
BL (0° – 30°)	142.7	28.3	B1		
BM (30° – 60°)	106.6	21.1	B0		
BH (60° – 80°)	2.7	0.5	B0		G0
BVH (80° – 90°)	0.1	0.0			G0
Upward	0	0.0			
UL (90° – 100°)	0.0	0.0		U0	
UH (100° – 180°)	0.0	0.0		U0	
Trapped Light	0	0.0			
Total Flux	504	100.0			



HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com


REPORT NUMBER: 17.02765
ISSUE DATE: 10/18/17
PREPARED FOR: PROGRESS
CATALOG NUMBER: P5674-3130K

PAGE: 8 OF 12

Zonal Lumen Summary

(Linear scale)

UH
0.0 lm
0.0%





HUBBELL
Lighting


701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 17.02765
ISSUE DATE: 10/18/17
PREPARED FOR: PROGRESS
CATALOG NUMBER: P5674-3130K

PAGE: 9 OF 12


Backlight Rating Details

(Logarithmic scale)




Glare Rating Details

(Logarithmic scale)



Uplight Rating Details

(Logarithmic scale)





HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 17.02765
ISSUE DATE: 10/18/17
PREPARED FOR: PROGRESS
CATALOG NUMBER: P5674-3130K

PAGE: 10 OF 12

CANDELA TABULATION

	TYPE	V
	90.0	0.
	87.5	0.
	85.0	0.
	82.5	0.
	80.0	1.
	77.5	1.
	75.0	1.
	72.5	2.
	70.0	2.
	67.5	3.
	65.0	4.
	62.5	5.
V	60.0	6.
E	57.5	15.
R	55.0	29.
T	52.5	43.
I	50.0	59.
C	47.5	76.
A	45.0	95.
L	42.5	115.
	40.0	136.
A	37.5	158.
N	35.0	181.
G	32.5	206.
L	30.0	233.
E	27.5	263.
	25.0	295.
	22.5	327.
	20.0	356.
	17.5	381.
	15.0	398.
	12.5	408.
	10.0	415.
	7.5	420.
	5.0	422.
	4.0<<	422.
	2.5	421.
	0.0	421.

CONE OF MAXIMUM CANDELA



HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 17.02765
ISSUE DATE: 10/18/17
PREPARED FOR: PROGRESS
CATALOG NUMBER: P5674-3130K

PAGE: 11 OF 12

5-DEGREE		
ZONAL	LUMEN	SUMMARY
0-	5	10
5-	10	30
10-	15	48
15-	20	62
20-	25	68
25-	30	67
30-	35	61
35-	40	53
40-	45	43
45-	50	31
50-	55	19
55-	60	7
60-	65	2
65-	70	2
70-	75	1
75-	80	1
80-	85	0
85-	90	0

10-DEGREE		
ZONAL	LUMEN	SUMMARY
0-	10	40
0-	20	151
0-	30	285
0-	40	399
0-	50	472
0-	60	499
0-	70	503
0-	80	504
0-	90	504

Project Number
17.02765



HUBBELL
Lighting

Date
10/13/2017

Goniophotometer Calibration

Calibration Lamp: GE 1000W, 120V, T6, CL (FEL)

Lamp Number: ITL78966-1000-38

Calibration Current: 8.300 Amps DC

Total Luminous Flux: 25889.0 Lumens

Calibration Date: 09/02/2016

Test Equipment Used

<i>Instrument</i>	<i>Manufacturer / Model</i>	<i>S/N</i>	<i>Calibration Due:</i>
<i>Goniophotometer</i>	ITL / HLI LAB 6 - Test Distance: 31.3'	N/A	N/A
<i>Power Analyzer</i>	Yokogawa / WT 332	C2QA27076V	11/2/2017
<i>Power Source</i>	Voltage-Regulated House Power	N/A	N/A
<i>Thermometer</i>	National Instruments / USB-TC01	1912745	11/7/2017

Sphere Calibration

Calibration Lamp: EIKO 28V75W/E10

Lamp Number: SCL-1400-J136

Calibration Current: 2.679 Amps

Total Luminous Flux: 1427 Lumens

Test Equipment Used - Color & SPD; THD & Power Factor

<i>Instrument</i>	<i>Manufacturer / Model</i>	<i>S/N</i>	<i>Calibration Due:</i>
<i>3-Meter Sphere</i>	Labsphere / LMS-3M	N/A	Calibrated Weekly
<i>Thermometer</i>	National Instruments / USB TC01	1912751	11/2/2017
<i>LAMP Power Meter</i>	Yokogawa / WT332	C2QA27075V	11/1/2017
<i>Power Supply</i>	Chroma / 61602	616020002113	N/A
<i>Power Supply PF/THD</i>	Voltage-Regulated House Power	N/A	N/A
<i>Aux Lamp Supply</i>	Labsphere / LPS-100-0833	0331159372	10/31/2017
<i>Cal Lamp Supply</i>	Labsphere / LPS-150-0268	1218148505	12/1/2017
<i>Spectrometer</i>	Labsphere / CDS 1100	0624117792	N/A

Hubbell Lighting, Inc.

701 Millennium Boulevard
Greenville, SC 29607
www.hubbellighting.com