

Project Number
P21.01663



HUBBELL
Lighting

Date
10/29/2021

Photometric Test Report

Lab 1
Sphere

Test Sample Description

Catalog Number: P560300 JAM-PE-19
Description: Wall Sconce with Paragon 6W Light Engine

Photometry

Test Method: IES LM-31-95
IES LM-79-08 §10
Preburn Time: 0:30
Time To Stabilize: 2:30
Total Operating Time: 4:00

Voltage (Volts): 119.9
Current (Amps): 0.056
Power (Watts): 6.1
Ambient Temp (°C): 24.8
PF @ 120V (%): 0.917
THD @ 120V (%): 44.4
PF @ 277V
THD @ 277V



Sphere

Test Method: IES LM-16-93
IES LM-79-08 §12.1
Preburn Time: 0:30
Time To Stabilize: 1:00
Total Operating Time: 1:30

Voltage (Volts): 120.0
Current (Amps): 0.055
Power (Watts): 6.0
Ambient Temp (°C): 24.3



Hubbell Lighting, Inc.

701 Millennium Boulevard
Greenville, SC 29607
www.hubbelllighting.com

Checked (sphere): Ben Lee
Checked (photometry): Connie Steadman
Approved: Philip McCarthy



** This customer-provided information was not verified by the laboratory and could affect the validity of the test results.*

Note that the LED manufacturer and part number are unverifiable by the lab.

This report shall not be reproduced, except in full, without the written approval of HLI's NVLAP-accredited laboratory

This report shall not be used to claim product certification, approval, or endorsement by NVLAP, NIST, or any agency of the federal government.





Lamp Cat#: CDAC-20-30135-120V-30 6W

Lamp Desc: 1 - Paragon 2700K LEDs

Efficacy: 41.3LPW

S/P Ratio: 1.3lm`/Lm

Spectral Results		
Name	Value	Unit
Radiant Flux	0.77	Watts
Lflux	248	Lumens
Scotopic Lumens	315	
Chrom x	0.4585	
Chrom y	0.4047	
Chrom u	0.2643	
Chrom v	0.3499	
Duv	0.0025	
Chrom u'	0.2643	
Chrom v'	0.5249	
CCT	2670	°K
Purity	59.1	%
Dominant Wavelength	585.1	nm
FWHM	107.2	
Peak Wavelength	607.3	nm
Lamda (Center)	604.2	nm
Centroid Wavelength	587.8	nm
SDCM		
RA	82	
Corr. Coef.	0.002097300	
Correlation	0.0054	
R1	82.9	
R2	96.1	
R3	89.1	
R4	78.6	
R5	83.9	
R6	95.3	
R7	77.6	
R8	55.1	
R9	8.5	
R10	91.5	
R11	78.7	
R12	80.3	
R13	86.6	
R14	94.7	









ANSI/IES TM-30-18 Color Rendition Report

Source: 21.01663

Manufacturer: PROGRESS

Date: 10/27/2021

Model: P560300 JAM-PE-19



Notes: This is a recommended method for displaying ANSI/IES TM-30-18 information.

x 0.4585
y 0.4047
u' 0.2643
v' 0.5249

CIE 13.3-1995
(CRI)

R_a 82
R_g 9



®

HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbelllighting.com

REPORT NUMBER: 21.01663

PAGE: 4 OF 14

ISSUE DATE: 10/14/21

PREPARED FOR: PROGRESS

CATALOG NUMBER: P560300 JAM-PE-19

LUMINAIRE: Wall Sconce with Paragon 6W Light Engine w/ Lens

LAMP CAT. NO.: CDAC-20-30135-120V-30 6W

LAMP: 1- Paragon 2700K LED

MOUNTING: Surface/Wall

NOTE: DATA SHOWN IS ABSOLUTE FOR THE SAMPLE PROVIDED.



HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbelllighting.com


REPORT NUMBER: 21.01663
ISSUE DATE: 10/14/21
PREPARED FOR: PROGRESS
CATALOG NUMBER: P560300 JAM-PE-19

PAGE: 5 OF 14

ISOFOOTCANDLE LINES OF HORIZONTAL ILLUMINATION Values based on 6-foot mounting height

IES Classification: (does not classify)
Cutoff Classification (deprecated): Full Cutoff

--- 1/2 Maximum Candela trace
X Maximum Candela point





HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 21.01663


ISSUE DATE: 10/14/21

PREPARED FOR: PROGRESS

CATALOG NUMBER: P560300 JAM-PE-19

PAGE: 6 OF 14

MAXIMUM PLANE AND MAXIMUM CONE PLOTS OF CANDELA






REPORT NUMBER: 21.01663
ISSUE DATE: 10/14/21
PREPARED FOR: PROGRESS
CATALOG NUMBER: P560300 JAM-PE-19

PAGE: 7 OF 14

COEFFICIENTS OF UTILIZATION AND FLUX DISTRIBUTION



	LUMENS	PERCENT OF FIXTURE
DOWNWARD STREET SIDE	163	62.3
DOWNWARD HOUSE SIDE	99	37.7
DOWNWARD TOTAL	262	100.0
UPWARD STREET SIDE	0	0.0
UPWARD HOUSE SIDE	0	0.0
UPWARD TOTAL	0	0.0
TOTAL FLUX	262	100.0

EFFICACY = 42.7 lm/W

ALL CANDELA AND LUMENS IN THIS REPORT ARE BASED ON ABSOLUTE PHOTOMETRY. THE COEFFICIENT OF UTILIZATION VALUES ARE BASED ON THE TOTAL ABSOLUTE LUMEN OUTPUT OF THIS LUMINAIRE SAMPLE.



HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbelllighting.com

REPORT NUMBER: 21.01663
ISSUE DATE: 10/14/21
PREPARED FOR: PROGRESS
CATALOG NUMBER: P560300 JAM-PE-19

PAGE: 8 OF 14

BUG Rating			B0 U0 G0		
Zonal Summary			Zone Ratings		
			B	U	G
Forward					
FL	(0° – 30°)	163			
FM	(30° – 60°)	53.5			
FH	(60° – 80°)	85.8			
FVH	(80° – 90°)	23.0			G0
		1.0			G0
Backward					
BL	(0° – 30°)	99			
BM	(30° – 60°)	46.7	B0		
BH	(60° – 80°)	45.6	B0		
BVH	(80° – 90°)	6.4	B0		G0
		0.2			G0
Upward					
UL	(90° – 100°)	0		U0	
UH	(100° – 180°)	0.0		U0	
Trapped Light					
Total Flux					
		0			
		262			
		100.0			



HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbellighting.com

REPORT NUMBER: 21.01663

ISSUE DATE: 10/14/21

PREPARED FOR: PROGRESS


CATALOG NUMBER: P560300 JAM-PE-19

PAGE: 9 OF 14

Zonal Lumen Summary

(Linear scale)

UH
0.0 lm
0.0%





HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbelllighting.com

REPORT NUMBER: 21.01663

ISSUE DATE: 10/14/21


PREPARED FOR: PROGRESS

CATALOG NUMBER: P560300 JAM-PE-19

PAGE: 10 OF 14


Backlight Rating Details

(Logarithmic scale)




Glare Rating Details

(Logarithmic scale)



Uplight Rating Details

(Logarithmic scale)





HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbelllighting.com

REPORT NUMBER: 21.01663

PAGE: 12 OF 14

ISSUE DATE: 10/14/21

PREPARED FOR: PROGRESS

CATALOG NUMBER: P560300 JAM-PE-19

CANDELA TABULATION

HOUSE SIDE		LATERAL ANGLE									
		95.0	105.0	115.0	125.0	135.0	145.0	155.0	165.0	175.0	180.0
VERTICAL	90.0	0.	0.	0.	0.	0.	0.	0.	0.	0.	0.
	87.5	1.	0.	0.	0.	0.	0.	0.	0.	0.	0.
	85.0	1.	0.	0.	0.	0.	0.	0.	0.	0.	0.
	82.5	1.	1.	0.	0.	0.	0.	0.	0.	0.	0.
	80.0	2.	1.	1.	1.	0.	0.	0.	0.	0.	0.
	77.5	5.	3.	1.	1.	0.	0.	0.	0.	0.	0.
	75.0	8.	6.	3.	2.	1.	1.	1.	0.	0.	0.
	72.5	13.	10.	5.	3.	2.	1.	1.	1.	1.	1.
	70.0	17.	13.	8.	4.	3.	2.	2.	2.	1.	1.
	67.5	22.	18.	11.	6.	4.	3.	3.	2.	2.	2.
	65.0	26.	22.	14.	9.	6.	4.	4.	3.	3.	3.
	62.5	31.	26.	18.	11.	7.	6.	5.	4.	4.	4.
	60.0	35.	30.	22.	14.	9.	7.	6.	5.	5.	5.
	57.5	40.	35.	26.	18.	12.	9.	8.	7.	7.	6.
	55.0	45.	41.	32.	22.	15.	11.	9.	8.	8.	8.
	52.5	51.	46.	38.	27.	19.	14.	11.	10.	10.	10.
	50.0	56.	52.	43.	32.	23.	17.	14.	12.	12.	11.
	47.5	62.	57.	50.	38.	28.	21.	17.	15.	14.	14.
	45.0	68.	64.	56.	45.	34.	26.	21.	18.	17.	17.
	42.5	75.	70.	63.	53.	42.	33.	27.	23.	22.	21.
ANGLE	40.0	81.	76.	70.	60.	50.	40.	33.	28.	27.	27.
	37.5	87.	83.	77.	68.	58.	48.	41.	36.	33.	33.
	35.0	93.	89.	84.	76.	67.	57.	49.	44.	42.	41.
	32.5	99.	95.	91.	84.	75.	66.	59.	53.	51.	51.
	30.0	104.	101.	98.	91.	84.	76.	69.	64.	62.	61.
	27.5	109.	107.	103.	98.	92.	85.	79.	75.	73.	71.
	25.0	115.	112.	109.	105.	100.	95.	90.	85.	84.	83.
	22.5	119.	117.	115.	112.	108.	103.	99.	96.	94.	94.
	20.0	124.	122.	120.	117.	115.	111.	108.	106.	104.	103.
	17.5	128.	126.	124.	122.	120.	117.	115.	113.	113.	112.
CONE OF MAXIMUM CANDELA	15.0	131.	129.	128.	126.	125.	123.	122.	120.	120.	120.
	12.5	134.	133.	132.	131.	129.	128.	127.	126.	126.	125.
	10.0	136.	135.	134.	133.	133.	132.	131.	131.	131.	130.
	7.5	138.	137.	137.	136.	135.	135.	134.	134.	133.	134.
	5.0	139.	139.	138.	138.	138.	138.	137.	137.	137.	137.
	3.0<<	141.	140.	140.	140.	140.	139.	139.	139.	139.	139.
	2.5	141.	140.	140.	140.	140.	140.	139.	139.	139.	139.
	0.0	141.	141.	141.	141.	141.	141.	141.	141.	141.	141.

CONE OF MAXIMUM CANDELA



HUBBELL
Lighting

701 Millennium Blvd
Greenville, SC 29607
www.hubbelllighting.com

REPORT NUMBER: 21.01663
ISSUE DATE: 10/14/21
PREPARED FOR: PROGRESS
CATALOG NUMBER: P560300 JAM-PE-19

PAGE: 13 OF 14

5-DEGREE		
ZONAL	LUMEN	SUMMARY
0-	5	3
5-	10	10
10-	15	16
15-	20	21
20-	25	24
25-	30	26
30-	35	27
35-	40	26
40-	45	24
45-	50	21
50-	55	18
55-	60	15
60-	65	12
65-	70	9
70-	75	6
75-	80	3
80-	85	1
85-	90	0

10-DEGREE		
ZONAL	LUMEN	SUMMARY
0-	10	13
0-	20	50
0-	30	100
0-	40	153
0-	50	198
0-	60	232
0-	70	253
0-	80	261
0-	90	262

Project Number
P21.01663



HUBBELL
Lighting

Date
10/29/2021

Goniophotometer Calibration

Calibration Lamp: EIKO 28V75W/E10
Lamp Number: SCL-1400-K136
Calibration Current: 2.679 Amps
Total Luminous Flux: 1429 Lumens

Test Equipment Used			
<i>Instrument</i>	<i>Manufacturer / Model</i>	<i>S/N</i>	<i>Calibration Due:</i>
Ambient Sensor	NI / USB-TC01	176F4E3	10/31/2021
Power Meter	Yokogawa / WT330	C2QA27071V	10/31/2022
Power Supply (DUT)	Voltage-Regulated House Power / Lab 1	N/A	N/A
Goniophotometer	ITL / HLI Lab 1- Test Distance: 31.74	N/A	8/28/2022

3-Meter-Sphere Calibration

Calibration Lamp: EIKO 28V75W/E10
Lamp Number: SCL-1400-K136
Calibration Current: 2.679 Amps
Total Luminous Flux: 1429 Lumens

Test Equipment Used - Color & SPD			
<i>Instrument</i>	<i>Manufacturer / Model</i>	<i>S/N</i>	<i>Calibration Due:</i>
Cal Lamp Supply	Labsphere/LPS-150-0268	1218148505	N/A
Aux. Lamp Supply	GWInstek / PSU 150-10	GER221028	N/A
Ambient Sensor	NI / USB-TC01	1912751	10/31/2022
Power Meter	Yokogawa / WT330	C2QA27072V	10/31/2022
Power Supply (DUT)	Chroma / 61602	61602002113	N/A
3-Meter Sphere	Labsphere / LMS-3M	N/A	10/31/2025
Spectrometer	Labsphere / CDS-1100	0624117792	10/31/2025

Test Equipment Used - THD & Power Factor			
<i>Instrument</i>	<i>Manufacturer / Model</i>	<i>S/N</i>	<i>Calibration Due:</i>
Power Meter	Yokogawa / WT330	C2QA27071V	10/31/2022
Power Supply (DUT)	Voltage-Regulated House Power / Lab 1	N/A	N/A

Hubbell Lighting, Inc.

701 Millennium Boulevard
Greenville, SC 29607
www.hubbelllighting.com

This report shall not be used to claim product certification, approval, or endorsement by NVLAP, NIST, or any agency of the federal government.

End of Report