



APPLICATION TABLE

Fuse Link		Single Phase Transformers			
Cat. No.	Amp. Rating	Full Load Amps	KVA Rating		
			2.4KV	4.8KV / 7.2KV / 14.4KV	
M0.2SF	0.2	0.21	-	1.5	
M0.3SF	0.3	0.31	-	1.5	
M0.4SF	0.4	0.42	-	3	
M0.6SF	0.6	0.63	1.5	3	
M0.7SF	0.7	0.69	-	5	
M1.0SF	1.0	1.04	5	7.5	
M1.3SF	1.3	1.25	3	10	
M1.4SF	1.4	1.39	-	10	
M1.6SF	1.6	1.56	-	7.5	
M2.1SF	2.1	2.08	5	15	
M3.1SF	3.1	3.13	7.5	15	
M3.5SF	3.5	3.47	-	25	
M4.2SF	4.2	4.17	10	25	
M5.2SF	5.2	5.21	25	37.5	
M6.3SF	6.3	6.25	15	75	
M7.0SF	7.0	6.95	-	50	
M7.8SF	7.8	7.81	37.5	100	
M10.4SF	10.4	10.42	25	75	
M14SF	14.0	13.9	37.5	100	
M21SF	21.0	20.9	50	100	
M32SF	32.0	31.3	75	167	
M46SF	46.0	41.7	100	250	
		46.3	-	333	
		52.2	-	250	

Slofast
MINIMUM
MELTING TIME

1/8 CYCLE - MINIMUM TIME FOR SAFE COORDINATION

MINIMUM MELTING TIME-CURRENT CHARACTERISTIC CURVES

For CHANCE TYPE SLOFAST Fuse Links. In CHANCE CUTOUTS

BASIS FOR DATA Standards NEMA PUB. NO. SG2. Dated MAY 1956

1. Tests made at LESS THAN 220 Volts a-c at LOW p-f., Starting at 25C with no initial load
2. Curves are plotted to MINIMUM Test points so variations should be PLUS

30040

