






| TRANSFORMER SPECIFICATIONS |                        |
|----------------------------|------------------------|
| PRIMARY VOLTAGE(S)         | 208/230/460            |
| SECONDARY VOLTAGE(S)       | 115                    |
| RATED V.A.                 | 50                     |
| RATED FREQUENCY            | 50/60                  |
| INSULATION CLASS           | 130°C @ MAX. RISE 55°C |
| AGENCY APPROVALS           | UL, CUL                |
| ESTIMATED WEIGHT           | 2.6 LBS                |



CONNECTION DIAGRAM

|  |  |            |
|--|--|------------|
| DIMENSIONS ARE IN INCHES<br>TOLERANCES:<br>.XX ± .03<br>.XXX ± .010<br>ANGULAR: ± 1° | NAME   | DATE       |
|  | DRAWN BY: VS   | 05/07/2020 |
| SOURCE N/A   | CHECKED BY:  |            |
| MATERIAL N/A   | PROPRIETARY AND CONFIDENTIAL   |            |
| FINISH N/A   | THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME IS PROHIBITED. |            |
| DO NOT SCALE DRAWING   |  |            |



DESCRIPTION:  
50 VA

SIZE DWG. NO. A TB50N005F0