



IDEA BOOK

The Idea Book for the Pro!



***Flexible Solutions
to Solve Almost Any
Manufacturing
Application Problem***



IDEA BOOK



Page #	File #	Title
2	951116	Versatile Bench Conveyor Support & Shelf Setup
3	980817	Neat & Tidy 36" Bench Back Aluminum Frame Provides Strength & Rigidity
4	991120	Bench Top Bridge Assemble with Ease!
5	961022	End of the Assembly Line Blues? Jibs with Balancers Could Be Your Answer!
6	980807	Quick JIBS WS50-MB Mounting Base Doubles as Boom Mount
7	030925	150 lb Jib for Big Tools
8	040524	150 lb Jib Provides Overhead Access
9	980504	300 lb Capacity Swing JIB Rugged I-Beam Boom Swings Full 360°
10	030716	Twin Booms Increase Productivity Puts Tools Where Needed
11	051023	Jib Kits Manage Multiple Air Tools & Cables
12	030731	Gantry Tool Crane Straddles Work Area or Assembly Line
13	051021	Put Balancer Over Work Area WS60 Tool Crane
14 & 15	971212	Support Up to 250 lbs! With Heavy Duty Overhead Crane
16	960404	Solve Problems with an Overhead Tool Crane
17	971213	Heavy Duty Continuous Tool Rails Provide 4 WAY Adjustment!
18	960715	Use Aluminum Track for Heavy Duty Continuous Tool Rail
19	960004	Build a Twin Rail Assembly Line Workstation
20	990505	Heavy Duty Tool Rail Hanger 250 lb Capacity Handles Even Heaviest Tools
21	951222	No Welding? Minimal Cutting? Aluminum Track to the Rescue!
22	960926	Beam Clamps Let You Mount Tool Rails to I-Beams
23	970227	Tool Rail Above Wire Harness Board
24	970116	Create a Workstation with a Traveling Boom
25	950612	No Kit That Fits? Make One! Here's How...
26	950613	Make Blind Riveting Easier With TORQ-ARM™
27	950614	Rivet Tool and TORQ-ATM™ Workstation Kit A Winning Combination
28	950831	TORQ-ATM™ For Trolley Mounting Installation & Adjustment
29 & 30	950906	Attach Pegboard to Workstations 2 Simple Ways
31	960530	Universal Base "Pocket" Workstation Mount
32	980429	Solve Wiring Logistics Issues With Mobile Wire Spool Cart
33	990805	Place 'n Pick Shelf Cart - Variety of Widths, Depths
34	990707	Test Bed Cart Mount Electrical Box, Other Test Equipment... Roll to Job
35	990805	Place 'n Pick Shelf Cart - Variety of Widths, Depths
36	980430	Adjustable Foot Rest Easy on the Legs!
37	960710	Connect Festoon Track to Beams with Welded Track Coupler
38	970109	360° Swivel Base Now Has Flexible Conduit Lead for Reel
39	970911	Put Mice to Work with Our Mouse Pad Tray
40	970912	Mounts Align Reels with Work
41	971125	Take a New Look With See-thru Modular Bin Racks!
42	980801	Keep Air Lines Out of the Way! Flexible & Coiled Air Lines for Workstations
43	981211	Shelf Fits Any Upright Spacing Positive Four Position Tilt Adds Flexibility
44	990115	Keyed Reel Mounting Plate Allows Welded Installation... Quick Removal/ Replacement
45	990507	LED Workbench Light
46	970123	Power Up... & Put Some Light on the Subject
47	991119	"Shock Stop" Prevents Cable Damage on "Over-powered" Balancers
48	051022	Easily Access Important Document

Hubbell Workplace Solutions products are so flexible that they can be used to solve almost any manufacturing application problem. So how can you use them?

Idea sheets! Each one shows you a new, better or different way to use Hubbell Workplace Solutions products. Some of these ideas came from our engineers trying to solve a customer's problem, others came from our customers showing us new ways to use existing products or components. Whenever they came from, they are all unique and interesting. Each Idea Sheet shows you a step-by-step "how to do it" procedure or a complete new kit that is now available but not yet cataloged.

Maybe you'll be saying:


"I wish I had thought of this years ago!"

Versatile Bench

WORKBENCHES

Conveyor Support & Shelf Setup

Here is an idea that could have broad application. Consider your customer's needs and the versatility of the new aluminum rail system and let your imagination run wild. This design features three shelves and a conveyor supported by the bench cross member. All frame components are standard except the length of some of the rails...cut those to fit shelf width. One could even use standard track nuts to fasten conveyor to rail.




BILL OF MATERIALS

ITEM	QTY.	DESCRIPTION	MODEL NO.
1	2	Rail, 36"	WA50-T036
2	2	Rail, 29"	WA50-T029
3	2	Rail, 72"	WA50-T072
4	2	Rail, 60"	WA50-T060
5	2	Rail, 29" (cut to two 13" lengths, 4 total pieces)	WA30-T029
6	6	Angle Bracket	WSAB
7	4	Corner Bracket	WA-CB
8	4	Leveler Foot	WA-LF
9	4	Top Mounting Bracket	WA-TMB
10	4	End Cap	WS50-EP

Neat & Tidy 36" Bench Back


Aluminum Frame Provides Strength & Rigidity

Many applications don't require a full workstation with tool rails over head. A vertical structure to hold tools and parts does the job quite adequately. For the strongest and most rigid small workbench back, use WA50 track, standard brackets and accessories. All components are right out of the catalog. The customer can supply a peg board or magnet/marker board. Add the hose reel as a finishing touch.




Bench Top Bridge

Assemble with Ease!



FRONT VIEW

SIDE VIEW






End of the Assembly Line Blues?

JIBS & BOOMS

Jibs with Balancers Could Be Your Answer!


Foam guns, staplers, glue guns...tools every bit as important as impact wrenches. Keep them out of the way yet always in reach, and make the "end of the line" people more productive, with tool jibs. Many variations possible.



QUICK Jibs

WS50-MB Mounting Base Doubles as Boom Mount

WS50 steel track or WA50 extruded aluminum track can easily and inexpensively be hung on standard 3" OD vertical columns to make jibs or rail supports. Height is fully adjustable. More than one "boom" can be mounted to each column, as shown in inset, below, or two booms can support longer track. May also be hung overhead using WS00-CC ceiling mounting columns. Maximum boom length with one end supported, 3'. Maximum capacity, 50 lbs.






150 lb Jib For Big Tools

Keeps Large Air or Electric Tools Suspended Overhead

Extra-heavy duty jib is ideal for Series "EH" balancers with heavy torque wrenches and similar equipment. Boom swings full 360° but swing may be limited by optional stops. 6', 8' or 10' boom is rugged WS60 rail with ladder reinforcing. Ten foot high vertical column is 4" o.d. schedule 40 pipe. Boom supported by tapered bearing and heavy-duty rollers. Includes wire rope festoon system with two trolleys.






150 lb Jib Provides Overhead Access

Swings Out of the Way When Not In Use

The 150 pound capacity extra-heavy duty jib is ideal for supporting large hose or cable. Boom swings out to perform task, stores flush with wall when not in use. Hose or cable easily mounted using cable clamps and suitable protective sleeves. If not installed next to wall, swing limiting stops must be used.






300 lb. Capacity Swing Jib

Rugged I-Beam Boom Swings Full 360°

If your plant uses large tools with air balancers, the Hubbell Workplace Solutions 300# Tool Jib is for you. It features a proven flanged wheel trolley rolling on an I-beam mounted to a tubular steel column. Air supply is conveniently handled by a swivel fitting at the top of the column and festoon trolleys leading to the balancer trolley. Boom swings full 360°, supported by heavy tapered roller bearing and two rollers.


DESCRIPTION	MODEL NUMBER
300 pound capacity swing tool jib	W6S-101002



Twin Booms Increase Productivity

Puts Tools Where Needed...Out of Way When Unneeded

If you need to put tools into the hands of people working some distance apart on a large product (the bow and stern of a boat, for example) take a close look at this twin boom jib. Each boom swings approximately 170° but cannot cross. Stops can be set to allow free swing or to lock boom in straight position and at every 15° in either direction. Unit is not available as a kit, but the individual parts (model numbers shown below) are listed in the Hubbell Workplace Solutions catalog.





Manage Multiple Air Tools & Cables

76.06

6-ft
BOOM

END CLIP
w/70 SERIES
SADDLE

TROLLEY
w/80 SERIES
BALANCER

TROLLEY
w/70 SERIES
SADDLE

APPROX. 12" DIAMETER LOOPS

BOOM LOCK
w/54
HANDLE

108.50

9-ft
COLUMN

46.55

76.29

100.18

Diagram illustrating the components and dimensions of the WS500 system:

- CUSTOMER'S STRUCTURE**: The top horizontal structure.
- WSB-xxxxx MOUNTING CHANNEL (OPTIONAL)**: The channel used for mounting the system.
- WS00-CC03 3-ft COLUMN**: The vertical support column.
- WS50-BTL TROLLEY w/WS00-CH FITTING**: The trolley assembly.
- 6-ft SWING BOOM**: The horizontal arm extending from the trolley.
- WS50-WS06**: The upper cable.
- 76.06**: The length of the swing boom.
- HWS-AL04 4-ft HOSE**: The hose connecting the trolley to the end clip.
- WS-EC02 END CLIP**: The clip used to secure the hose.
- 13.76**: The vertical distance from the floor to the trolley.
- TQ1507 BALANCER**: The balancer component.
- CS-F2 HANGER SADDLE**: The saddle used for hanging the tool.
- HWS-AL06 6-ft HOSE**: The hose connecting the balancer to the tool.
- AIR TOOL BY OTHERS**: The air tool being used.
- 144.00**: The total height from the floor to the top of the mounting channel.
- 95.91**: The height from the floor to the bottom of the mounting channel.
- FLOOR**: The ground level.

IDEA-FILE #051023




Gantry Tool Crane

CRANES & RAILS

Straddles Work Area or Assembly Line


This highly versatile gantry tool crane can be assembled from standard components and kits. Capacity varies depending on which components are used. A 50 lb. capacity crane uses WS-50 components and a WS50-ET05 or WS50-ET06 tool crane kit. The rugged 250 lb. capacity unit is assembled from WS-60 components and a WS60-ET06 tool crane kit. To maintain full 250 lb. capacity, the rails on which the crane runs must be no more than 72" in length. Longer spans will decrease capacity. The cranes are designed to provide overhead tool support and are NOT designed for lifting. All but the casters are shown in the WS catalog. WS50 components have bake polyester finish. WS60 components are galvanized or zinc plated.



Put Balancer Over Work Area


WS60 Tool Crane Reaches Out to Task

Originally designed to facilitate removal of cast aluminum car wheels from casting machines, the structure below was constructed from standard components (the WS60-ET09 tool crane is not cataloged but is available). In addition to its original use, it is ideal for heavier tools used on assembly lines and similar applications. Total rail length can be customized to fit the job. The one shown here is 36' long. Maximum capacity, including balancer plus tool or air hoist plus load is 85 lbs. Using two or more tool cranes is not recommended unless there is some provision to prevent the cranes from coming too close together. This could overload the rail structure. Obviously, the columns must be securely and appropriately anchored (suggested anchoring details are provided with each column).



Support Up to 250 lbs! With Heavy Duty Overhead Crane

Rugged bridge crane allows overhead handling of extra-capacity tools with maximum safety and minimum cost. Uses proven components which mount to rugged WS60 rails. Available in 6' or 12' kits.




Tool Crane mounts in two WS60 rails. Rails must be parallel and level to allow free travel of crane and must be supported every 6' (1.9m). Recommended distance between support rails is length of tool rail less 12" (305mm). Tool rail and reinforcing rail may be cut if shorter length required. Do not span more than 72" (1829mm) without reinforcing rail installed. **MAXIMUM RATED CAPACITY OF TOOL CRANE is 250 lbs (112.5 kg) including tool, balancer, and attachments.** Unit depth is 37.875" (962mm) bumper-to-bumper. See reverse side for attachments and assembly details.

MODEL CHART


DESCRIPTION	MODEL NUMBER
250 lb. capacity O.H. Tool Crane 72"(1829mm) long tool rail Max. rail spacing 60"(1524mm)	WS60-ET06
250 lb. capacity O.H. Tool Crane 144"(3658mm) long tool rail Max. rail spacing 132"(3353mm)	WS60-ET12

MORE →

Assembly Details




Accessories



Solve Problems with an Overhead Tool Crane

Rugged bridge crane allows overhead tool handling with maximum safety and minimum cost. Uses proven components which mount to standard WS-50 or WA-50 rails. Available as complete kits to speed assembly.



Tool Crane mounts in two WS50 rails. Rails must be parallel and level to allow free travel of crane. Recommended distance between support rails is length of tool rail less 12" (305mm). MAXIMUM RATED CAPACITY OF TOOL CRANE is 50 lbs (22.5 kg) including tool, balancer, and attachments. Unit depth is 24.25" (616mm) bumper-to-bumper.

Overhead Tool Crane includes (4) WS50-06TP plain trolleys, (2) WS50-ETK tool track bridges, (2) WS50-HG hanger brackets, (2) WS-EP end caps, (2) WS50-ES end stops, (1) WS50-BTL Labyrinth tool trolley, (1) WS50 tool rail (length per model) and all assembly hardware.

MODEL CHART

DESCRIPTION	MODEL NUMBER
O.H. Tool Crane, 48" long tool rail	WS50-ET04
O.H. Tool Crane, 60" long tool rail	WS50-ET05
O.H. Tool Crane, 72" long tool rail	WS50-ET06
O.H. Tool Crane, 108" long tool rail	WS50-ET09
O.H. Tool Crane, 144" long tool rail	WS50-ET12


NOTE: For best results, crane width should not exceed six (6) times trolley wheelbase. Example: 24"(2 ft.) x 6 = 12 ft.



Heavy Duty Continuous Tool Rails

Provide 4 WAY Adjustment!


Dual tool rails running entire length of 60' conveyor are spanned by multiple 24" long rolling rails with balancer trolleys. Easily reaches all areas of conveyor surface. Extruded Aluminum vertical supports fit perfectly into sleeves on the 30" or 36" bottom plates or WS50-MB mounting bases. Also recommended, for added stability, is the LEG BOX, model #WS50-SCB. Single 60' rail with numerous balancer trolleys could also be used.



* Leg Box bolt to aluminum upright and to conveyor or bench leg, greatly increasing structure rigidity.

Use Aluminum Track for Heavy Duty Continuous Tool Rail


While HWS Extruded Aluminum Track will not fit into the "coupler" on the top of WS50-UFxx BENCH LEG BASES, it fits perfectly into the sleeve on the bottom plate (as it does on all other mounting bases). It's not cataloged, but the bottom plates, both 30" and 36", are available separately. Order model #WS50-UF30B (30") or #WS50-UF36B (36"). Also available separately is the LEG BOX, model #WS50-SCB. List prices below.



Build a Twin Rail Assembly Line Workstation

Any Length! Aluminum Rail Makes it Versatile!

There could be an infinite number of variations on this theme so use your imagination. Be sure to stay within the following size and capacity parameters: Maximum 10' wide and 8' (6' is ideal) between uprights, 50 lbs. maximum per trolley and no more than one trolley per upright. Design the structure to be as long as needed. Aluminum rail is available in 20' lengths, but make sure splice angles don't interfere with hanger disks.






Heavy Duty Tool Rail Hanger

250 lb Capacity Handles Even Heaviest Tools

Listed here are the components needed for a hanging 250 lb. capacity tool or festoon rail. Three of them are new... the WS60-MB Mounting Base, the WS60-HC Hanger Coupler, and the WS60-HW Bolt Kit. The rest are listed in WS-5 catalog. Thru bolts both top and bottom (see photo) act as a safety net. Thru bolts are included with the mounting bases. These components will not be sold as a kit because the galvanized C-60 Track, both vertical and horizontal, can vary greatly in length. Track must be supported every six feet to preserve 250 lb. capacity rating.




DESCRIPTION	MODEL NO.
Mounting Base for C-60 Track	WS60-MB
C-60 Hanger Coupler	WS60-HC
Hardware Kit*	WS60-HW

*Hardware Kit includes (4) 1/2 x 1 1/2 bolts, nuts, lock washers and flat washers required to attach hanger coupler to mounting base.

No Welding? Minimal Cutting?

Aluminum Track to the Rescue!



NEED: Continuous tool rail over 18' conveyor.

SOLUTION: HWS Extruded Aluminum Track with standard brackets eliminates the welding required with steel. Two leveling feet (turned "out") on each upright allow bolting to floor. Angle bracket attaches to conveyor. Can be used equally well on continuous benches.

PARTS LIST

ITEM	QTY.	DESCRIPTION	PART NO.
1	4	RAIL-9' (CUT FROM 20' RAIL)	WA50-N240
2	4	RAIL-6'	WA50-N072
3	4	RAIL-23" (CUT TO LENGTH)	WA50-N029
4	12	ANGLE BRACKET	WS-AB
5	8	45° ANGLE BRACE	WA50-NB17
6	16	ANGLE BRACE BRACKET	WA-AB
7	8	LEVELER FOOT	WA-LF
8	8	HANGER DISK	WA-HD
9	2	RAIL-18' (CUT TO LENGTH)	WA50-N240
10	12	END CAP	WS50-EP
11	A/R	BALANCER TROLLEY	WS50-BTL
N/S	4	END STOP	WS50-ES

REMOVE THIS TRACK NUT AND BOLT ANGLE BRACKET TO CONVEYOR SUPPORT


TURN TWO LEVELER FEET OUTWARDS AND BOLT TO FLOOR

Beam Clamps Let You Mount Tool Rails to I-Beams


No Drilling or Welding!

Now you can quickly and accurately hang and align WS50 tool rails beneath or beside beams. Model **#WS50-BCH Beam Clamp Hanger Bracket** or separate Model **#WS-BC Beam Clamp** (with track nut) require no drilling or welding. Hanger Brackets attach to beam flanges from 2.625" to 5.25" wide. Beam Clamps affix WS50 support arms to top flange (Figure 3) or WA50 aluminum track to bottom flange perpendicular to or at an angle to beam (Figure 2). All components are zinc plated.


**MODEL #WS50-BCH
Beam Clamp Hanger**




**MODEL #WS-BC
Beam Clamp**



**Figure 1
TOOL RAIL BENEATH I-BEAM,
PARALLEL TO BEAM**



**Figure 2
ALUMINUM TOOL RAIL BENEATH I-BEAM,
PERPENDICULAR (BEAM-TO-BEAM)**




**Figure 3
TOOL RAIL BESIDE I-BEAM, ONE OR BOTH SIDES**

Tool Rail Above Wire Harness Board

The **PROBLEM**: Keep the tools used in assembling wire harnesses always within easy reach.

The **SOLUTION**: An aluminum tool rail (could be steel with traditional hanger brackets) hung from WS50 supports. Support structures fastened to back of board by WS50-MP Universal Bases bolted to existing stand uprights. Sure beats laying the tools on five gallon pails as was done previously.






Create a Workstation with a Traveling Boom

WORKSTATION KITS

Add Reach & Flexibility!

The **PROBLEM**: Move a 30 lb. tool to any spot on a 40 ft. assembly line, including in or out 8+ ft.


The **SOLUTION**: Two aluminum rails hung beneath fixed jibs mounted on 11 ft. columns. WS50-10HR rolling hangers with side guide rollers inserted into the rails. Then, two 9 ft. aluminum rails hung from the trolleys and a third WS50-10HR trolley with CVS-11 swivel clevis in one of those rails. DOES IT WORK? You bet it does.



No Kit That Fits? Make One!

Here's How...

Workstation kits in the catalog stop at 6' width. But, you don't have to stop there. When your customer has benches wider than 6', put together your own design using components from the **HWS** catalog. Shown here are the components used to assemble a workstation for use on an **8' to 9' wide bench**. A similar procedure would be used for other bench sizes.



BILL OF MATERIALS

QTY.	DESCRIPTION	MODEL NO.
2	5 ft. WS50 Rail	WS50-T05
2	Angle Bracket	WS-AB
2	3 ft. WS50 Rail	WS50-T03
1	9 ft. WS50 Rail	WS50-T09
1	9 ft. WS30 Rail	WS30-T09
1	Table Bracket-L.H.	WS50-BBL
1	Table Bracket-R.H.	WS50-BBR
2	WS50 Hanger Bracket	WS50-HG
2	WS30 Hanger Bracket	WS30-HG
2	WS50 End Stop	WS50-ES
2	WS30 End Stop	WS30-ES
6	WS50 End Cap	WS50-EP
2	WS30 End Cap	WS30-EP
1	WS50 Balancer Trolley or	WS50-BTL
1	WS30 Balancer Trolley	WS30-BTL

Make Blind Riveting Easier

With TORQ-ARM™

- ✓ Tool easily connected
- ✓ No tool dropping
- ✓ Tool kept vertical
- ✓ Hoses stay aligned
- ✓ Mandrel discharge reliable




Illustration shows how two popular brands of blind rivet tools with a TORQ-ARM™ can improve the work area. See **Hubbell Workplace Solutions** catalog for details on Workstation Kits and Components.


*Supplied by others.



Rivet Tool & TORQ-ARM™ Workstation Kit

A Winning Combination

- ✓ Highly versatile tool platform
- ✓ Tool easily connected
- ✓ One model number ordering
- ✓ Tool always within reach
- ✓ Increased productivity




Economy and ease of installation plus the versatility of a TORQ-ARM Workstation Kit add up to winning performance in blind rivet assembly applications. (You can find the kit in the WS catalog.) Be sure to order model with 2.0 - 5.0 pound capacity. Lobster brand attaches with no modifications to TORQ-ARM. Simply remove the U-joint manifold to install the POP brand.

*Supplied by others.

TORQ-ARM™ For Trolley Mounting

Installation & Adjustment




INSTALLATION

- 1- Slide trolley into rail. **NOTE:** WS30-xx TORQ-ARMS go into WS30 rails. WS50-xx TORQ-ARMS go into WS50 rails.
- 2- Install end stop and end cap into rail. Securely tighten bolts clamping end stop to rail.


WARNING

Improperly tightened end stop bolts could result in damage to equipment or personal injury.

- 3- Install tool onto TORQ-ARM and connect air line.
- 4- Adjust tool balancer for desired action.




ADJUSTING BALANCER



- 1- Increase tension by turning adjustment knob clockwise.



- 2- Decrease tension by pushing button on top of balancer. One click equals 1/5 turn of adjustment knob.




- 3- Adjust drag so that tool remains in desired "hands off" position. Increase drag by turning screwdriver clockwise. Decrease drag by turning screwdriver counterclockwise.


Attach Pegboard to Workstations

2 Simple Ways

#WS-UH UNIVERSAL BRACKETS were designed with peg board in mind. Peg board may be bolted to front of brackets (below, left) or behind tabs (below right). Either way, slots in brackets fit holes in peg board for bolting.




Method of Attaching Brackets to Columns



MORE 

Alternate Pegboard/Workstation Attachment


For added stiffness on wider workstations, use **#WS50-BB0x** BIN BARS top and bottom. Peg board is bolted to back. Four inch on center slots in bin bars fit holes in peg board. Use flat washers both sides.



Universal Base “Pocket” Workstation Mount

UNIVERSAL BASE “POCKET” WORKSTATION MOUNT

The Universal Base (#WS50-MP) works well on some benches and is often ideal for use on conveyors. Unique clamp plate prevents WS50 column from sliding through.






Solve Wiring Logistics Issues

MOBILE CARTS

With Mobile Wire Spool Cart

Here's the answer to production or maintenance wiring jobs. Roll the wire to the job, unspool what you need, and return the cart to a convenient storage place. Made of strong but light **WA50** aluminum rail with formed steel brackets, the cart measures 54" high, 36" deep and 33.6" wide. There is a 27" clear space between spool shaft brackets, which are fully adjustable. The cart is available with four heavy-duty casters (two fixed and two swivel with locks), two fixed casters and two glides or, for semi-permanent installation, with four glides. Swivel casters may be installed at either front or back. All components, except hardware, finished with chip-resistant baked polyester coating. Rails are beige and brackets are black. Some assembly required. **MAXIMUM CAPACITY: 300 lbs.**




DESCRIPTION	MODEL NUMBER
Wire spool cart with four casters.	HWP-RC01
Wire spool cart with four glides.	HWP-RC02
Wire spool cart with two fixed casters and two glides.	HWP-RC03



Put a Workstation Wherever You Need It!

With Push 'n Place™ Workstation

Here's a way to maintain flexibility on the plant floor without sacrificing safety and productivity. The Hubbell Workplace Solutions *Push 'n Place* portable workstation moves to where the action is. It rolls easily on four heavy-duty locking, swivel casters. Constructed of light but strong extruded aluminum rail, it measures 36" deep and 90" high, including casters. Frame is 44" wide o.c., perfect for under a 5' conveyor section, while the tool bar is 60" long and can be fitted with splice angles to adjoin two or more units. Bin Bar, air manifold and balancer trolley with fitting plus 3/8" hose are standard. Frame is finished with beige baked polyester. Brackets are matt black.




Test Bed Cart

Mount Electrical Box, Other Test Equipment...Roll to Job

Bar holds box bins for miscellaneous storage. Frame is strong extruded aluminum with beige baked polyester finish. All joining brackets are heavy steel with matte black polyester. Includes four locking, swivel casters and all assembly hardware. Bin boxes, electrical box and cables not included. Some assembly required.



MODEL
NUMBER
HWP-TC01





PLACE 'n PICK™ Shelf Cart

Now Available in Variety of Widths, Depths

Do you ever need five or six foot wide* shelves on a mobile unit? Or, 18" deep shelves? Perhaps two shelves and a Bin Bar... or six Bin Bars, three on each side? How about adding a Power Bar for electrical power or a Manifold for air? Use your imagination.

Now it's possible to construct a Mobile Shelf Cart to exactly fill your requirements. Pick either the complete kit (HWP-SCxx) which includes three 12" x 30", 42", 54", or 66" shelves, aluminum frame, cover strip for the slots, four swivel casters, and all hardware... or choose the size frame that will fit your needs and equip it with either 12" or 18" deep shelves and any of numerous workstation accessories.

The basic frames, available in 3', 4', 5' and 6' widths*, are constructed of sturdy aluminum with heavy steel brackets. All assembly hardware is included. Shelves, which must be ordered to fit cart width, may be either 12" or 18" deep. Other standard accessories such as Bin Bars, Power Bars, and manifolds are easily added to the frame. Cover strip is not included with the frame kits but may be ordered separately. Bin boxes are **not** included. Below is a list of most components, including prices.

*NOTE: Nominal dimensions. Actual shelf width between uprights is 6" less than nominal over all cart width; i.e., 6' wide unit has 66" wide shelves.



Shelf Cart with Bin Boxes
(Boxes not included)

KIT & COMPONENT LISTING

DESCRIPTION	MODEL NO.
Complete Cart Kit-(3) 12"D x 30"W Shelves included.	HWP-SC30
Complete Cart Kit-(3) 12"D x 42"W Shelves included.	HWP-SC42
Complete Cart Kit-(3) 12"D x 54"W Shelves included.	HWP-SC54
Complete Cart Kit-(3) 12"D x 66"W Shelves included.	HWP-SC66
Frame Kit-For 30" Wide Shelves.	HWP-SC03
Frame Kit-For 42" Wide Shelves.	HWP-SC04
Frame Kit-For 54" Wide Shelves.	HWP-SC05
Frame Kit-For 66" Wide Shelves.	HWP-SC06
Shelf-12"D x 30"W.	WS50-SS03
Shelf-12"D x 42"W.	WS50-SS04
Shelf-12"D x 54"W.	WS50-SS05
Shelf-12"D x 66"W.	WS50-SS06
Shelf-18"D x 30"W.	WS50-SS183
Shelf-18"D x 42"W.	WS50-SS184
Shelf-18"D x 54"W.	WS50-SS185
Shelf-18"D x 66"W.	WS50-SS186
Bin Bar-36" (Fits 30"W Frame Kit).	WS50-BB03A
Bin Bar-48" (Fits 42"W Frame Kit).	WS50-BB04A
Bin Bar-60" (Fits 54"W Frame Kit).	WS50-BB05A
Bin Bar-72" (Fits 66"W Frame Kit).	WS50-BB06A
Power Bar-36" Power Strip/36"Mounting Bar.	WPB-303A
Power Bar-36" Power Strip/48"Mounting Bar.	WPB-304A
Power Bar-60" Power Strip/60"Mounting Bar.	WPB-505A
Power Bar-60" Power Strip/72"Mounting Bar.	WPB-506A
Cover Strip-20' long roll. Field cut to length.	WA-CS20




Adjustable Foot Rest

ACCESSORIES

Easy on the Legs!



Seated or standing, your workers can be more productive and more comfortable when a foot rest is used. In addition, use of a foot rest offers a degree of protection from back or leg strain. Fully adjustable and strong enough for heavy industrial applications, it's constructed of steel with extruded aluminum foot bar. Standard model measures 29" wide, 12.75" deep and 12.25" high. Smaller "under desk" version measures is 23" wide. Both rest on four non-skid rubber feet. The foot bar is easily adjustable from 4" to 11" above the floor and tilts 15° fore and aft. Frame is finished with matte black baked polyester coating. Foot bar is natural aluminum with two anti-skid strips.

DESCRIPTION	MODEL NUMBER
Standard Adjustable foot rest	HWS-FR01
Office "under desk" foot rest	HWS-FR02





Connect Festoon Track to Beams with Weldable Track Coupler


When is a track coupler more than a coupler? When it's the new *notched* festoon track coupler. It joins track sections, but also doubles as a sleeve that can be welded onto I-beams or crane boxes to support track or create tow arms. The notch on one end clears radii or weld. Simply remove two set screws and weld it in place. Zinc plated.



AFFIXING TRACK TO I-BEAM



AFFIXING TRACK TO CRANE BOX






360° Swivel Base Now Has Flexible Conduit Lead for Reel

360° SWIVEL BASE NOW HAS FLEXIBLE CONDUIT LEAD FOR REEL


An 18" flexible conduit is now included with models SB360-430, SB360-830 and SB360-455 swivel bases for the G14 and G16 electric cable reels. Lead wires, pre-connected to the slip rings in the base, are long enough for easy connection in the reel junction box. Best news of all...there is no price increase.





Put Mice to Work with Our Mouse Pad Tray

When your computer terminal or PC has a mouse, it needs a place to live. Developed in cooperation with one of the leading manufactures of personal computers, the Hubbell Workplace Solutions Mouse Pad Tray attaches quickly to the keyboard supports on your swing arm mounted computer tray. It makes the mouse easy to reach and use. Plus, the tray's recessed design keeps your mouse safe in a manufacturing environment.




Easy to install. All hardware included.

NOTE: May require that holes be drilled in older keyboard supports. Cannot be installed on units without keyboard supports.


Mounts Align Reels with Work

Wear and tear on cord or cable is greatly reduced when the reel is aligned so the guide faces the direction of pull. These reel mounts allow the reel to turn toward the work and pivot or swing if the cord or hose is moved from side to side during use. Both are designed for use with the GL series Industrial Quality Cord Reels or GRC series Compact Hose Reels



Reel that does not pivot or swing with side-to-side motion places undue stress on cord or hose as well as reel. Result: Increased wear and shortened life.



Properly mounted reel pivots or swings as cord or hose travels side-to-side. Straight pull off reel improves operation, increases life of reel and cord or hose.




WALL MOUNTED SWING BASE Model RC-WP





**MOUNTING PLATE
TO WALL
DIMENSIONS**

Wall Mounted Swing Base allows reel to pivot 180°. Made of heavy steel, base features positive stops to prevent reel from contacting wall and porous bronze bushings. Fits all GL and GRC reels.




340° PIVOT BASE Model RC-PB-B



**MOUNTING PLATE
DIMENSIONS**

Heavy duty steel 340° Pivot Base allows reel to follow cord or hose. Base features positive stop to prevent over travel which could tangle input lines. May be mounted with reel base facing up or down. Fits all GL and GRC reels.

Take a New Look With See-Thru Modular Bin Racks!



SWINGING BIN RACK may be affixed to column or bench mounted swing arm bases, with or without arms or elbows. Available in three models, pictured below. Maximum rated capacity, including bins and contents, is 30 lbs. Accepts most standard bin boxes (not included). Bin bars are 18"(457mm) wide. Vertical track is 12"(305mm) high for single and double bar models, 24"(610mm) high on triple bar model. Black baked polyester finish. All hardware included.




FIGURE 1
Single Bin Bar
#W5BR-1018




FIGURE 2
Double Bin Bar
#W5BR-2018





FIGURE 3
Triple Bin Bar
#W5BR-3018




ASSEMBLY AND ADJUSTMENT IS QUICK AND EASY



Keep Air Lines Out of the Way!

Flexible & Coiled Air Lines for Workstations

The purpose of tool trolleys on workstation rails is to allow the tool to be easily moved to the work position. Stiff, unyielding hoses prevent free trolley movement and can actually increase work effort. Hubbell Workplace Solutions 1/4" ID coiled hose is designed to run from the trolley fitting to the tool. It stays up, out of the way yet is so flexible you will hardly know it's there. For connecting fitting on tool trolley to air supply or manifold select the strong, flexible, 3/8" ID air lines. Available in eleven lengths, they feature swivel fittings at both ends for minimal trolley interference.



A **Coiled hose from trolley to tool.** Transparent blue polyurethane hose is flexible and light weight, doesn't interfere with tool positioning. Excellent memory retention. High chemical resistance. 3/8" O.D. x 1/4" I.D. x 4' extended length. 1/4" NPT male swivel fitting one end; fixed male fitting opposite end.

DESCRIPTION	MODEL NUMBER
Coiled hose 3/8"od x 1/4"id x 4' Blue polyurethane	HWS-AC04




B **The most flexible air line we have found.** Ideal for connecting tool trolley to manifold or other supply because its flexibility does not interfere with trolley movement. Clear, reinforced plastic, 3/8" I.D. with 3/8" NPT male swivel fittings on both ends.

LENGTH		MODEL NUMBER
ft.	(m)	
2	(0.6)	HWS-AL02
3	(0.9)	HWS-AL03
4	(1.2)	HWS-AL04
5	(1.5)	HWS-AL05
6	(1.8)	HWS-AL06

Shelf Fits Any Upright Spacing

Positive Four Position Tilt Adds Flexibility

New design positions shelf in front of, not between, supporting uprights. This allows almost unlimited upright spacing, dictated by the bench design not shelf length. Shelf attaches to uprights with track nuts (like old style) and has adjustable tilt (also like old style). New design, however, features positive four position tilt with holes rather than slots. Brackets attach to shelf with track nuts into lateral rail welded to underside of shelf. Four models are available, fitting workstations with upright column center-to-center spacing to 68" (1727mm). Baked polyester finish is beige on shelf and matt black on brackets. Shelf includes black end caps.




MODEL NUMBER	MAX. UPRIGHT SPACING center-to-center	
WS50-SS03A	32"	(812mm)
WS50-SS04A	44"	(1117mm)
WS50-SS05A	56"	(1422mm)
WS50-SS06A	68"	(1727mm)

Keyed Reel Mounting Plate

Allows Welded Installation...Quick Removal/Replacement

The model RTD-KM1 kit facilitates mounting of 14" and 16" hose or cable reels to vertical surfaces...walls, posts, etc. Reel is quickly and easily attached to mounting plate by sliding keyways and slots onto bolts which are then tightened to hold the reel securely in place. Removal is just as easy. The kit is especially useful when a welded installation is desired...only the plate, not the reel base, need be welded in place. Kit consists of one Post (or wall) Plate, one Reel Plate and hardware for attaching reel plate to reel and for hanging reel on post plate. Hardware for mounting post plate not included. Plates have durable matte black baked-on polyester finish. **NOTE:** Overhead mounting on horizontal support (ceiling) is not recommended. **Safety bolt**, included, **must be installed if mounted on horizontal surface.**






4 Ft LED Workbench Light

4000 Lumen LED, 3500K

This new workstation light is designed to give you greatest light on the work at minimal cost. Available in either 2' or 4' length, both models feature **four T8 fluorescent lamps** with polycarbonate safety tubes, electric starters, 10' grounded cords for easy plug-in, and parabolic louvers to direct light where you need it. Lights include mounting brackets for easy attachment to workstation rail. NOTE: Brackets do not provide for tilt or width adjustment.



DESCRIPTION	MODEL NO
24" Fluorescent Light Fixture with four T8 lamps	WBL-402
48" Fluorescent Light Fixture with four T8 lamps	WBL-404




POWER UP...

& Put Some Light on the Subject

Here's a fitting touch to your workplace: a fluorescent, overhead work light and a power bar. Both are custom designed for use on Hubbell Workplace Solutions workstations. **Light** has adjustable mounting brackets and uses two 48" fluorescent T8 lamps (included). **Power Bar** is available in two lengths; 36" with six grounded outlets and 60" with ten outlets. Both feature on/off switch and circuit breaker with reset button. Available with or without mounting bar. Light includes 10' cord and power bar includes 6' cord with standard 110 volt grounded plugs.

NEW, IMPROVED LIGHT. ALL THESE FEATURES AT NO INCREASE IN PRICE.

- Polycarbonate safety tubes protect lamps, increase safety and prevent contamination if lamp breaks.
- Rotary locking lamp holders accept two T8 lamps.
- Custom brackets allow two mounting options.
- Light tilts 15° fore or aft. Allows you to direct light where needed.
- Blacked-out side lens minimizes stray light.





“SHOCK STOP” to the Rescue *Prevents Cable Damage on “Over-powered” Balancers*


Cable breakage on tool balancers is extremely rare because of the tough, extremely durable nylon coated steel aircraft cable used. On most failure reports we receive, the cable breaks at the eye or, more precisely, just above the clip that is swaged around the cable to form the eye. Two of the primary causes of cable failure on Series BG balance reels are better classified as user error...(1) overtensioning the spring, and (2) allowing the tool to “slam” back into the balancer from a fully extended or near fully extended position. In most reported cases, both of these conditions are present.

The result of this “overtensioned slamming” is that the cable stop is slowly pushed down the cable until it is against the eye and can go no farther. Then, every time the tool is returned to the raised position the cable stop hits against the reel housing but the tool tries to keep moving, causing the cable to bend at the point between the stop and the eye. Bend any cable in the same place enough times and it will fatigue and break.

The most obvious way to prevent this type of cable damage is better customer education. With a product as simple to use as a balancer, however, this isn’t always easy. The customer buys the balancer, hangs it and a variety of people use and adjust it.

Now there is a mechanical means of minimizing this type of cable damage. We call it the **“Shock Stop”**. It consists of a new fixed stop, a compression spring and a second cable stop which has been milled out so it can’t grip the cable and thus slides easily. The kit is easily installed by removing the existing stop, threading the eye through the spring, and installing the two new stops with the “slider” on top.

Shock Stop can be used on any model Series BG balancer. It is not needed on the smaller Series BD balancers.




DESCRIPTION	MODEL NO
Shock Stop for tool balancers	BG-SH




Easily Access Important Document

When safety and efficiency matter, having the proper information easily accessible on the shop floor is very important. Qualtech Document Stands allow for files such as prints, drawings, production orders, instructions or safety guidelines to be kept clean, safe and organized right at your fingertips. We do offer a stand made especially for **MSDS - Right-to-Know** documents - Model A1200 Series. We offer many different types of stands with different mounting options. See our catalog for more information or call our office.



Model 1200S





IDEA BOOK



Formerly known as Hubbell Workplace Solutions, Tool Assist Pro from Hubbell helps companies increase productivity through highly effective ergonomics for worker and plant safety.

Safe environments increase profitability by reducing the direct and indirect costs of work-related injuries and accidents. This also contributes to improved employee morale. Plus, companies save money by preventing tools from being broken lost or stolen.

Any business in any industry that uses tools can benefit from Tool Assist Pro solutions.



Gleason Reel Corp.
Mayville, WI 53050
920-387-4120
www.hubbell.com/gleasonreel/en